



Part Number : 1301370153
Product Description : Super-Safeway Cordset
14 Gauge SOOW, 2 Pole/3 Wire, Cordset
Length 7.62m (25.0'), NEMA L5-20 125V
Series Number : 130143
Status : Active
Product Category : Wiring Devices
Engineering Number : 2647A143



Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Wiring Devices
Series	130143
Description	Super-Safeway Cordset 14 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 7.62m (25.0'), NEMA L5-20 125V
IP Rating	N/A
NEMA Configuration	NEMA L5-20
Product Name	Super-Safeway
Specialty	N/A
Type	Cordset
UPC	78678870463

Agency

CSA	LR6837
UL	E38085

Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	125V

Physical

Cord Type	14/3 SOOW
Flange	No
Flip Lid	No
Gender	Male-Female
Length	7.62m (25.0')
Lighted Connector	No
Locking Blade	Yes
Net Weight	211.000/kg
Poles	2-pole/3-wire
Receptacle Type	Single

This document was generated on Apr 26, 2025