

P/N: T911633ACC

Copyright

© 2023, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

Document identity

Publ. No.: T911633ACC

Commit: 60018

Language:

Modified: 2019-10-02

Formatted: 2023-04-04

Website

<http://www.flir.com>

Customer support

<http://support.flir.com>

Disclaimer

Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to exportquestions@flir.com with any questions.



General description	
Power supply, with multi plugs.	
Power system	
AC operation	100–240 VAC, 50/60 Hz, 12 VDC out
Power	3000 mA at 12 VDC
Physical data	
Size (L × W × H)	90 × 54 × 38 mm (3.5 × 2.1 × 1.5 in.)
Cable length	1.2 m (3.9 ft.)
Shipping information	
Packaging, type	Cardboard box
List of contents	• Power supply including cable • EU plug • UK plug • US plug • AU plug
Packaging, weight	280 g (0.62 lb.)
Packaging, size	150 × 70 × 70 mm (5.9 × 2.8 × 2.8 in.)
EAN-13	4743254003194
UPC-12	845188014599
Country of origin	China

Compatible with the following products:

- 10101-0101; FLIR G304 14.5°
- 10101-0102; FLIR G304 24°
- 10201-0101; FLIR G306 14.5°
- 10201-0102; FLIR G306 24°
- 10301-0102; FLIR G615 20°
- 10401-0101; FLIR Gx320 14.5°
- 10401-0102; FLIR Gx320 24°
- 10501-0101; FLIR G620 14.5°
- 10501-0102; FLIR G620 24°
- 10601-0101; FLIR Gx620 14.5°
- 10601-0102; FLIR Gx620 24°
- 10701-0101; FLIR G635 14.5°
- 10701-0102; FLIR G635 24°
- 10801-0101; FLIR G343 14.5°
- 10801-0102; FLIR G343 24°
- 10901-0101; FLIR G346 14.5°
- 10901-0102; FLIR G346 24°

P/N: T911633ACC

© 2023, FLIR Systems, Inc.

#T911633ACC; r. 60018;

- 85201-0102; FLIR GF77 LR 25°
- 85202-0102; FLIR GF77 HR 25°
- 85203-0102; FLIR GF77 LR 25° + HR 25°
- 85204-0102; FLIR GF77 LR 25° + LR 6°
- 85205-0102; FLIR GF77 HR 25° + HR 6°
- 85206-0102; FLIR GF77 LR 25° + HR 25° + HR 6°
- 85207-0102; FLIR GF77 LR 25° + HR 25° + LR 6°
- 85208-0102; FLIR GF77 LR 25° + HR 25° + LR 6° + HR 6°
- 79301-0101; FLIR T530 14°
- 79302-0101; FLIR T530 24°
- 79304-0101; FLIR T530 24° + 14°
- 79306-0101; FLIR T530 24° + 14° & 42°
- 79305-0101; FLIR T530 24° + 42°
- 79303-0101; FLIR T530 42°
- 79307-0101; FLIR T530 42° + 14°
- 79308-0101; FLIR T530 Dual FOV 14° + 24°
- 79301-0201; FLIR T540 14°
- 79302-0201; FLIR T540 24°
- 79304-0201; FLIR T540 24° + 14°
- 79306-0201; FLIR T540 24° + 14° & 42°
- 79305-0201; FLIR T540 24° + 42°
- 79303-0201; FLIR T540 42°
- 79307-0201; FLIR T540 42° + 14°
- 79308-0201; FLIR T540 Dual FOV 14° + 24°
- 79302-0302; FLIR T540-EST 24°
- 79303-0302; FLIR T540-EST 42°
- 89001-0101; FLIR T560 14°
- 89002-0101; FLIR T560 24°
- 89004-0101; FLIR T560 24° + 14°
- 89006-0101; FLIR T560 24° + 14° & 42°
- 89005-0101; FLIR T560 24° + 42°
- 89003-0101; FLIR T560 42°
- 89007-0101; FLIR T560 42° + 14°
- 89009-0101; FLIR T560 Dual FOV 14° + 24°
- 89002-0302; FLIR T560-EST 24°
- 89003-0302; FLIR T560-EST 42°
- 82501-0201; FLIR T840 14°
- 82502-0201; FLIR T840 24°
- 82504-0201; FLIR T840 24° + 14°
- 82506-0201; FLIR T840 24° + 14° & 42°
- 82509-0201; FLIR T840 24° + 14° & 6°
- 82505-0201; FLIR T840 24° + 42°
- 82508-0201; FLIR T840 24° + 6°
- 82503-0201; FLIR T840 42°
- 82507-0201; FLIR T840 42° + 14°
- 82510-0201; FLIR T840 Dual FOV 14° + 24°
- 89201-0101; FLIR T860 14°
- 89202-0101; FLIR T860 24°
- 89204-0101; FLIR T860 24° + 14°
- 89206-0101; FLIR T860 24° + 14° & 42°
- 89211-0101; FLIR T860 24° + 14° & 6°
- 89205-0101; FLIR T860 24° + 42°
- 89210-0101; FLIR T860 24° + 6°
- 89203-0101; FLIR T860 42°
- 89207-0101; FLIR T860 42° + 14°
- 89212-0101; FLIR T860 Dual FOV 14° + 24°
- 89201-0201; FLIR T865 14°
- 89202-0201; FLIR T865 24°
- 89204-0201; FLIR T865 24° + 14°



Power supply for battery charger

P/N: T911633ACC

© 2023, FLIR Systems, Inc.

#T911633ACC; r. 60018;

- 89206-0201; FLIR T865 24° + 14° & 42°
- 89213-0201; FLIR T865 24° + 14° & 6°
- 89205-0201; FLIR T865 24° + 42°
- 89212-0201; FLIR T865 24° + 6°
- 89203-0201; FLIR T865 42°
- 89207-0201; FLIR T865 42° + 14°
- 89214-0201; FLIR T865 Dual FOV 14° + 24°
- 84502-0301; FLIR E52 24°
- 84512-1201; FLIR E54 24°
- 84512-2102; FLIR E54-EST 24°
- 78511-1101; FLIR E76 14°
- 78512-1101; FLIR E76 24°
- 78514-1101; FLIR E76 24° + 14°
- 78516-1101; FLIR E76 24° + 14° & 42°
- 78515-1101; FLIR E76 24° + 42°
- 78513-1101; FLIR E76 42°
- 78517-1101; FLIR E76 42° + 14°
- 78511-1301; FLIR E86 14°
- 78512-1301; FLIR E86 24°
- 78514-1301; FLIR E86 24° + 14°
- 78516-1301; FLIR E86 24° + 14° & 42°
- 78515-1301; FLIR E86 24° + 42°
- 78513-1301; FLIR E86 42°
- 78517-1301; FLIR E86 42° + 14°
- 78521-2102; FLIR E86-EST 24°
- 78522-2202; FLIR E86-EST 42°
- 90201-0101; FLIR E96 14°
- 90202-0101; FLIR E96 24°
- 90204-0101; FLIR E96 24° + 14°
- 90206-0101; FLIR E96 24° + 14° & 42°
- 90205-0101; FLIR E96 24° + 42°
- 90203-0101; FLIR E96 42°
- 90207-0101; FLIR E96 42° + 14°