



MICRO SWITCH
 FREEPORT, ILLINOIS, U.S.A.
 A DIVISION OF HONEYWELL

FED. MFG. CODE 91829

SWITCH-BASIC


CATALOG LISTING

BZ-R173-P4

X28854
 ISSUE 2

CATALOG LISTING
BZ-R173-P4
 PAGE 1 OF 1
 RELEASE NO. SR 12358
 REPLACES
M
 ISSUE 9

REVISIONS	
A	SR12358
B	RER JUN 66
C	CO22797
D	SD 27 APR 67
E	CO22889
F	MBF 16 MAY 67
G	CO 34775
H	GLH 10 FEB 75
I	CO 73287-G
J	JAL 20 OCT 93
K	CO 75367B
L	KDR 3 MAR 94
M	CO 77863
N	GJW 1 MAY 96
O	203222
P	CST 5 JUN 01



3X 8-32 UNC (.219) BINDING HEAD COMBINATION TERMINAL SCREW AND CUPWASHER

NOTE -
 ▲ MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE — — — — 7 - 10 OZ	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
DIFFERENTIAL FORCE — — 1/2 - 1 1/4 OZ	L111 15A 125, 250 OR 277 VAC 1/8HP 125 VAC, 1/4HP 250 VAC	UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES
DIFFERENTIAL TRAVEL — — — .0005 MAX	CE	TOLERANCES ARE:
OVERTRAVEL — — — .005 MIN	L288 L299 L306	ONE PLACE (.0) ± .030 TWO PLACE (.00) ± .018 THREE PLACE (.000) ± .008 ANGLES ±
	16A 250V T85 5E4	WEIGHT .074 LB

RASTER
 DRAWN
 RER 9 MAY 66
 CHECK GCH
 CO-80376

