

Part Number : [190670087](#)


Product Description : NylaKrimp Funnel Entry Ring
Tongue Terminal for 4 AWG Wire, Stud Size 5/8" (M16),
Carton

Series Number : 19067

Status : Active

Product Category : Ring and Spade Terminals

Engineering Part Number : F-969-58



Documents and Resources

Drawings

[190670087 sd.pdf](#)

Specifications

[PS-19902-013-001.pdf](#)

[PS-19902-016-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19067
Description	NylaKrimp Funnel Entry Ring Tongue Terminal for 4 AWG Wire, Stud Size 5/8" (M16), Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	NylaKrimp
Style	Ring
Type	Ring Terminal
UPC	800753066595

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Flammability	94V-2
Insulation	Nylon (PA)
Material - Plating Mating	Tin
Net Weight	13.348/g
Packaging Type	Carton
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	5/8" (M16)
Termination Interface Style	Crimp or Compression

Wire Insulation Diameter	12.95mm max.
Wire Size (AWG)	4

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for 8-2 AWG Terminals	<u>640013900</u>
Hand Crimp Tool for 4 AWG Insulated Ring Terminals	<u>640017870</u>

This document was generated on Apr 14, 2026