

2100at SSD

MTFDHBK064TDP-1AT12AIYY part detail

Documents

+ Data Sheet
+ Reach Statement
+ RoHS

Specifications

Capacity	Sequential READ	Sequential WRITE	READ Performance	WRITE Performance	Interface
64GB	2000 MB/s	1800 MB/s	2000 MB/s	1800 MB/s	4000 MB/s

Operating Temp	Part Status Code	Module Box Qty	Package Dimension (W x L x H) mm	Package Type	Module Version
-40C to +95C	Production	250	16.00 x 20.00 x 1.20	GREEN	M.2

Product Name	Technology
2100AI	TLC