


COIL: 26.5 VDC NOMINAL

WINDING #1	WINDING #2
1000 OHMS ± 10%	1000 OHMS ± 10%
13V MUST OPERATE	13V MUST OPERATE

ENVIRONMENT:


VIBRATION 10 CPS TO 2000 CPS @ 20 g's

SHOCK 50 g's 11 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES: LATCH & RESET TIME : 4 MS MAX.
CONTACT BOUNCE : 2 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: 2 AMPS / 30 VDC

DR. R.B. 12/15/92 | CK. JAW 12-15-92

COMMUNICATIONS INSTRUMENTS, INC.

CUST. HI-G
CUST. NO. 2KL-2A-126

TYPE "LS" RELAY

LS-9108

Downloaded from Arrow.com.