

Representative Image

Catalog No. TC5828

Description: 2WAY MTG BASE .89X.4IN NAT NYL SCR

UPC No 786210873596

Home > Wire & Cable Management > Deltec > Cable tie mounts

Four-Way Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 22.48mm (0.885 Inches), Width of 10.16mmn (0.40 Inches), Height of 3.8mm (0.15 Inches), Screw Mounting Method, #8 Hex Head Screw, Mounting Hole Diameter of 4.3mm (0.17 Inches), 100 Pack

Descriptors

Category	Cable tie mounts
Special Features	These mounting bases can be used to tie bundles running parallel or perpendicular to length of base.

Specifications

Number Of Entries	2
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

Classifications

Brand Name	Ty-Rap

Dimensions

Mount Size	#8

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000449 Mounting base and -element for cable ties
Length	22.48 mm
Length	0.89 inch
Width	10.16 mm
Width	0.4 inch
Height	3.8 mm

by ABB

Downloaded from Arrow.com.

ETIM	EC000449 Mounting base and -element for cable ties
Height	0.15 inch
Type of fastening	Other
Diameter mounting hole	4.3 mm
Material	Plastic
Material quality	Polyamide (PA)
Colour	Natural colour

Downloaded from Arrow.com.