



Pushing Performance
Since 1945

RJ45 RJ45 jack 1 Gbit PoE 27,5 mm




Image is for illustration purposes only. Please refer to product description.

Part number	09 45 551 1531
Specification	RJ45 RJ45 jack 1 Gbit PoE 27,5 mm
HARTING eCatalogue	https://harting.com/09455511531

Identification

Category	Connectors
Series	HARTING RJ Industrial®
Identification	Magnetics
Element	Female
Specification	RJ45
	with integrated transformer
	Angled
	With light pipe

Version

Termination method	Wave soldering termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8

Technical characteristics

Rated voltage	60 V DC
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
Limiting temperature	-40 ... +85 °C
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP20

Material properties

RoHS	compliant
------	-----------



Pushing Performance
Since 1945

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

UL / CSA	UL 1977 DUXR2.E254191
	CSA-C22.2 No. 182.4, No. 233-09 DUXR8.E254191
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	9.43 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140224513
eCl@ss	27460201 PCB connector (board connector)
ETIM	EC002637
UNSPSC 24.0	39121415