



Part Number : 1301370147  
Product Description : Super-Safeway Multiple  
Outlet Box, Standard Depth, 2-Sided, Cord  
Clamp, Box only  
Series Number : 130137  
Status : Active  
Product Category : Power Distribution  
Engineering Number : 3050



Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
--------	--------

Category	Power Distribution
Series	130137
Description	Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, Cord Clamp, Box only
Enclosure Rating	NEMA 4
NEMA Configuration	N/A
Product Name	Super-Safeway
Type	Multiple Outlet Box
UPC	78678875056

## Agency

CSA	LR6837
-----	--------

## Electrical

Current - Maximum per Contact	Per Cust. Supplied Receptacle
GFCI	No
GFCI Reset	N/A
Ground Continuity Monitor	No
Open Neutral Relay	N/A
Voltage - Maximum	Per Cust. Supplied Receptacle

## Physical

Cord Diameter	8.26-16.64mm (.325-.655")
Cord Grip Body Size	F4 1"
Cord Length	N/A
Cord Type	N/A
Feed-Thru	No
Flip Lid	No
Material - Housing	Rubber
Mounting Style	Portable
Number of Receptacles	2 - Customer Supplied
Packaging Type	Carton
Receptacle Type	N/A

---

This document was generated on Apr 22, 2025