

4-Port USB Charging Station with OTG Hub - 5V 6A / 30W USB Charger Output

MODEL NUMBER: **U280-004-OTG**



Description

Tired of searching for wall outlets or swapping out one device to charge another? Tripp Lite's U280-004-OTG Charging hub with OTG is the solution, featuring four ports for charging tablets, phones, or other mobile devices, all at the same time. It provides a single location to charge multiple devices, and its sleek, compact design keeps your charging area neat and clutter free. It features two 5V, 2A ports and two 5V, 1A ports, providing up to 6A for charging the connected devices. Furthermore, it comes with an internal power supply, eliminating the need to fumble around with bulky power adapters. When not being used for charging, it doubles as a USB OTG hub. Simply connect your OTG compatible tablet or phone to the dedicated port on the hub, and then connect up to four USB devices (flash drive, mouse, keyboard, etc.). You can now use those devices on your tablet or phone. So whether you're at home or in the office, our Charging Hub with OTG provides an ideal solution for charging your devices or expanding the functionality of your OTG compatible tablet or phone. Input: 100-240V, 50/60Hz, 1.0A / Output: 5V 6A

Features

- Features four ports for charging tablets, phones, or other mobile devices in a single location
- Includes two 5V, 2A ports and two 5V, 1A ports
- Doubles as a USB OTG Hub when not being used for charging; connect up to four USB devices (flash drive, mouse, keyboard, etc.) to your OTG compatible tablet or phone
- All four ports are USB Battery Charging (BC) specification v1.2 compliant. Supports iPad; iPhone; Samsung Galaxy (Tab, Phone, and Note); Microsoft Surface; and more
- Sleek, compact design keeps charging area neat and clutter free
- Features Over-Temperature and Over-Current detection and protection
- Internal power supply eliminates the need to fumble around with bulky power adapters
- Input: 100-240V, 50/60Hz, 1.0A / Output: 5V 6A
- P059-006 (EU) and P061-006 (UK) power cords (sold separately) available for international use

Highlights

- Charge up to 4 tablets, phones, or other mobile devices
- Features two 5V, 2A ports and two 5V, 1A ports
- Doubles as a USB OTG Hub; connect up to four USB devices (flash drive, mouse, keyboard, etc.) to your OTG compatible tablet or phone
- All four ports are USB Battery Charging (BC) specification v1.2 compliant. Supports iPad; iPhone; Samsung Galaxy (Tab, Phone, and Note); Microsoft Surface; etc.
- Sleek, compact design keeps charging area neat and clutter free
- Input: 100-240V, 50/60Hz, 1.0A / Output: 5V 6A

Package Includes

- U280-004-OTG
- Micro-USB OTG Cable - 2.6-ft.
- C7 to NEMA 1-15P Power Cord - 3.9-ft.
- Quick Start Guide



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Specifications

OVERVIEW	
UPC Code	037332182937
Product Type	Plug in Charger
Charging Form Factor	Charging Hub
Device Compatibility	Phone; Tablet; Amazon Kindle
Technology	USB
INPUT	
Nominal Input Voltage(s) Supported	120V AC; 230V AC
Plug Type	C7 to NEMA 1-15P
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Input Frequency	50/60Hz
Input Plug Type	NEMA 1-15P (NON-POLARIZED)
Input Current	120V (0.8A) / 230V (0.4A)
OUTPUT	
Output Capacity	5V 6A
Overload Protection	Yes
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (Power)
CHARGING	
Charging Ports / Amps	(2) 1A; (2) 2A
Number of Charging Ports	4
Total Charging Amps	6A
Charging Method	USB
Total Charging Watts	30
Charging Port Type	(4) USB A (FEMALE)
Charging Method Detail	5V - 1.5A (7W)
PHYSICAL	
Color	White
Material of Construction	Polycarbonate



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / cm)	5.59 x 24.13 x 15.24
Shipping Dimensions (hwd / in.)	2.20 x 9.50 x 6.00
Shipping Weight (kg)	0.41
Shipping Weight (lbs.)	0.90
Unit Dimensions (hwd / cm)	3.05 x 10.414 x 9.91
Unit Dimensions (hwd / in.)	1.2 x 4.1 x 3.9
Unit Packaging Type	Box
Unit Weight (kg)	0.20
Unit Weight (lbs.)	0.45
ENVIRONMENTAL	
Operating Temperature Range	41 to 95 F (5 to 35 C)
Storage Temperature Range	-4 to 122 F (-20 to 50 C)
Relative Humidity	20% to 80% RH, Non-Condensing
Power Consumption (Watts)	37.7
Power Consumption Detail	37.7W (Operating) 0.07W (Standby)
CONNECTIONS	
Ports	5
Side A - Connector 1	NEMA 1-15P (NON-POLARIZED)
Side A - Connector 2	USB A (FEMALE)
Side B - Connector 1	(4) USB A (FEMALE)
SPECIAL FEATURES	
Overcurrent Protection	Yes
Overvoltage Protection	Yes
GaN Technology	No
STANDARDS & COMPLIANCE	
Certifications	Tested to UL 60950-1: 2007, CAN/CSA-C22.2 No. 60950-1:07, IEC 60950-1, EN55022, EN55024, FCC Class B, RoHS
Approvals	UL Listed
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>