

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0536270274

Status:

Active

Overview:

SlimStack Board-to-Board/Board-to-FPC Connectors

Description:

SlimStack Board-to-Board Connector, 0.635mm Pitch, 0.635 Series, Plug, 10.00 or 16.00mm Mated Height, 6.40mm Mated Width, 20 Circuits

Documents:

- [Drawing \(PDF\)](#)

[3D Model \(PDF\)](#)

[3D Model](#)

[Product Specification 527600000-000 \(PDF\)](#)

[Packaging Specification SPK-53627-001-001 \(PDF\)](#)
- [Datasheet \(PDF\)](#)

[Product Guide \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Reference Guide \(PDF\)](#)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Comments

Overview

Product Name

Series Name

UPC

PCB Headers

53627

Board-to-Board, Signal

Stacking-Type

SlimStack Board-to-Board/Board-to-FPC Connectors

SlimStack

0.635, Floating

822348164493

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Glow-Wire Capable

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Mated Height

Mated Width

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Number of Rows

Orientation

PCB Locator

PCB Retention

Packaging Type

Pitch - Mating Interface

Polarized to PCB

Robotic Placement

Shrouded

Temperature Range - Operating

Termination Interface: Style

No

20

20

Brown

50

No

No

No

None

Yes

10.00mm, 16.00mm

6.40mm

Copper Alloy

Gold

Tin

579.461/mg

2

Vertical

Yes

Yes

Embossed Tape on Reel

0.64mm

Yes

Metal Cap

Fully

-55° to +105°C

Surface Mount

Electrical

Current - Maximum per Contact

0.5A



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

53627 Series

Mates With

SlimStack 0.635 Receptacle [52885](#) , [52901](#)

Voltage - Maximum	100V
Material Info	
Reference - Drawing Numbers	
Packaging Specification	SPK-53627-001-001
Product Specification	527600000-000
Sales Drawing	SD-53627-001-001, SD-53627-002-001

This document was generated on 01/05/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION