








5. ORIENTATION OF "DEUTSCH" AND "-EP14" TO BE OPTIONAL.
4. BORDER SIGNIFIES THAT PINS 1,2,6 AND PINS 3,4,5 ARE BUSSED TOGETHER WITH 3 PIN BUSBARS.
3. THIS DT04-6P-EP14 MATES WITH DT06-6S-**** (**** = ALL MODIFICATIONS). CONSULT FACTORY FOR MODIFICATIONS.
2. DIMENSIONS ARE $\pm .025$ [0.63] UNLESS OTHERWISE SPECIFIED.
1. DIMENSIONS ARE IN INCHES [MILLIMETERS].

NOTES:

REV
NC DT04-6P-EP14

REVISIONS			
SYM	DESCRIPTION	DATE	APPROVED
NC	NEW RELEASE PER E.O. PI6141	9/2/89	(Signature)

6. THE 3 PIN BUSBAR HAS A MAXIMUM CURRENT RATING OF 13 AMPS.

SIGNATURE & DATE		CP		MATL. CODE
DR	M. GONZALEZ 7/7/99	DT 6 WAY RECEPTACLE (2) 3 PIN BUSBARS-NICKEL PLATED COLOR: BLACK		The Deutsch Company DEUTSCH I.P.D. 3850 INDUSTRIAL AVE. HEMET, CALIF. 92545
CHK	(Signature) 7/2/99			
PE	(Signature) 7/2/99			
APPD	(Signature) 9/2/89			
SCALE	NONE	WT		
		ENVELOPE		
		DWG SIZE	CODE 11139	SHEET OF