

Toolless Cat6a Keystone Jack, Gray, TAA

MODEL NUMBER: BHDBT-001-KJ-GY



Terminate the Cat6a wall jack in your HDBaseT installation without using a punchdown tool. Ideal for standard keystone wallplates.

Description

The BHDBT-001-KJ-GY Toolless Cat6a Keystone Jack terminates the Cat6a wall jack in your HDBaseT installation without using a punchdown tool. Just lace the conductors into the stuffer cap, press the 110 connector, and lock the jack into place. Use in standard keystone wallplates with any Cat6a cable. This jack is UL-listed and meets all requirements for EIA/TIA Cat6a compliance.

Features

Optimal Solution for HDBaseT Installations where Patching is a Must!

- Cat6a design is built for ultra-fast performance
- Works with standard keystone wallplates
- Terminates your Cat6a wall jack without using a punchdown tool
- Compatible with all Cat6a cables

Superior Construction for Superior Performance

- UL-listed
- Meets all EIA/TIA Cat6a requirements

TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchasing

Specifications

OVERVIEW	
UPC Code	037332190499
Technology	Cat5/5e; Cat6; Cat6a; HDBaseT

Highlights

- Easy to terminate—no punchdown tool required
- Keystone design for use with standard data wallplate
- Compatible with all Cat6a cables
- Meets all EIA/TIA Cat6a requirements

Package Includes

- BHDBT-001-KJ-GY Toolless Cat6a Keystone Jack, Gray

PHYSICAL	
Color	Gray
Shipping Dimensions (hwd / in.)	5.00 x 4.00 x 0.50
Shipping Dimensions (hwd / cm)	12.70 x 10.16 x 1.27
Shipping Weight (lbs.)	0.04
Shipping Weight (kg)	0.02
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
CONNECTIONS	
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	110 IDC
PoE Type	Type 4 High-Power (100W, IEEE 802.3bt)
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty