



Part Number : [1300950186](#)
Product Description : Medium Duty Wire Mesh
Pulling Grip, Single/Double Weave, Bale Eye, Standard
Mesh Length 0.914m (36.00"), Approximate Break
Strength 11113.01kg (24500 lbs)
Series Number : 130095
Status : Obsolete
Product Category : Cable Grips
Engineering Part Number : 35955

Documents and Resources

Drawings
[1300950186 sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Cable Grips
Series	130095
Description	Medium Duty Wire Mesh Pulling Grip, Single/Double Weave, Bale Eye, Standard Mesh Length 0.914m (36.00"), Approximate Break Strength 11113.01kg (24500 lbs)
Comments	Cable Eye Thickness 1/2"
Product Name	Medium Duty
Type	Pulling Grip
UPC	78678835955

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	11113.01kg (24500 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	76.20-88.65mm (3.000-3.490")
Color - Grommet	N/A
Eye Type	Flexible
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.914m (36.00")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A