



Representative Image

**Catalog No. 5342****Description: 1/2 IN INSUL 45 DEG LIQ TIGHT CON****UPC No 786210053424****Home > Cable Protection Systems > T&B Liquidtight Fittings > Liquid tight connectors**

1/2 Inch 45 Degree Malleable Iron Insulated Liquidtight Connector

**Descriptors**

Category	Liquid tight connectors
Application	Used where flexible metal raceway is installed in outdoor or indoor locations where exposed to continuous or intermittent moisture.

**Specifications**

Material	Malleable Iron
Finish	Electro Zinc Plated/Chromate Coating

**Classifications**

Brand Name	T&B Liquidtight Fittings
Standard	UL E23018, CSA

**Dimensions**

Size	1/2 Inch
------	----------

**Compliance and Certifications**

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1/2 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other

**by ABB**

ETIM	EC001180 Screw connection for protective metallic hose
One-piece	N
Material housing	Other
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y