

Part Number : [191640054](#)

Product Description : Perma-Seal Snap Receptacle for 16-14 AWG Wire, Diameter 3.96mm, Carton

Series Number : 19164

Status : Active

Product Category : Quick Disconnects

Engineering Part Number : SBRB-8156N



Documents and Resources

Drawings


[191640054 sd.pdf](#)

Specifications

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19164
Description	Perma-Seal Snap Receptacle for 16-14 AWG Wire, Diameter 3.96mm, Carton
Product Name	Perma-Seal
Type	Snap Receptacle
UPC	800753113398

Agency

UL	E152602
----	---------

Electrical

Voltage - Maximum	600V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Blue
Gender	Female
Glow-Wire Capable	No
Insulated	Fully
Insulation	NiAc
Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon

Net Weight	1.597/g
Orientation	Straight
Packaging Type	Carton
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Tab Thickness	N/A
Tab Width	N/A
Temperature Range - Operating	-55° to +125°C
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.81mm max.
Wire Size (AWG)	14, 16
Wire Size mm ²	1.00-2.50

Application Tooling

Global

Description	Part Number
Hand Crimp Tool	<u>640014900</u>

This document was generated on May 04, 2026