





FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH-BASIC



CIRCUIT DIAGRAM



NOTE -



MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000±.002 CENTERS
SUITABLE ONLY FOR APPLICATIONS IMPARTING A
RAPID STROKE TO THE SWITCH PLUNGER

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE — — — 9 OZ MAX	CONTACT ARRANGEMENT (SEE CIRCUIT DIAGRAM)	DO NOT SCALE PRINT
RELEASE FORCE — — — 1 OZ MIN	UNDERWRITERS' LAB. INC. LISTED RATING 15 A-125, 250, OR 480 VAC -L73- 1 A-125 VDC; 0.5 A-250 VDC 1/4 HP-125 VAC; 1/2 HP-250 VAC	UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES TOLERANCES ARE:
DIFFERENTIAL TRAVEL — — .175 MAX		ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ±
DO NOT OVERTRAVEL MORE THAN — .060		WEIGHT

BZ-3ALT1

N

**DRAWING
NUMBER**

4

AN

REVISIONS

A	OBS C025587
---	----------------

K J A
11 APR 69

☐ REINSTATT

D B W
26 JAN 72

C 21 JUN 73

CO32577

D	PR-3609
B	C

ОСТ 73

E 69351-0
JWB

18 JUL 91
E 0013541

0015541	TSG
---------	-----

31 MAY 05	
-----------	--

--	--

--	--

[illegible]

--	--

11/11/2011

--	--

10

1

100

A W N

8 DR.

3037

—80378