

**Part Number :** [936000016](#)

**Product Description :** Heavy-Duty Metal Cable Gland - 5 Bar, for 8.00-14.00mm Cable, Pg16 Thread

**Series Number :** 93600

**Status :** Active

**Product Category :** Heavy-Duty Cable Glands

**Engineering Part Number :** 7000.6827.0



---

## Documents and Resources


### Drawings

[936000016\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Not Relevant  |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant  |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21  |
| REACH SVHC         | Not Contained per D(2025)7771-DC (04 Feb 2026)  |
| EU RoHS            | Compliant with Exemption 6(c) per EU 2015/863   |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

[CE - Declaration of Conformity](#)

[UKCA - Declaration of Conformity](#)

## Part Details

### General

|                  |   |
|------------------|---|
| Status           | Active  |
| Category         | Cable Glands  |
| Series           | 93600   |
| Description      | Heavy-Duty Metal Cable Gland - 5 Bar, for 8.00-14.00mm Cable, Pg16 Thread |
| Cable Gland Type | IP68 - 5 Bar  |
| IP Rating        | IP68  |
| Product Name     | Heavy-Duty Connectors   |
| UPC              | 887191820989  |

### Physical

|                               |                |
|-------------------------------|----------------|
| Cable Diameter                | 8.00-14.00mm   |
| Material - Cable Gland        | Brass          |
| Material - Plating            | Nickel         |
| Packaging Type                | Bag            |
| Panel Cutout Diameter         | 22.80mm        |
| Temperature Range - Operating | -40° to +125°C |
| Thread Size                   | Pg16           |
| Thread Type                   | (Pg)           |
| Waterproof / Dustproof        | Yes            |
| Waterproof / Dustproof Type   | IP68           |

## Mates With / Use With

### Use with Part(s)

| Description | Part Number |
|-------------|-------------|
|-------------|-------------|

|          |   |
|----------|---|
| Use With | Industrial connector hoods and housings |
|----------|---|

---

This document was generated on May 04, 2026