



Part Number : [1301110030](#)

Product Description : Safety Yellow Molded Stringlight, 200W, 12/3 SJTW with 2.43m Lead, 10 Sockets, Full Ground Ring, Overall Length 30.48m (100.0')

Series Number : 130111

Status : Active

Product Category : Lamps and Lights

Engineering Number : 5002



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130111
Description	Safety Yellow Molded Stringlight, 200W, 12/3 SJTW with 2.43m Lead, 10 Sockets, Full Ground Ring, Overall Length 30.48m (100.0')
NEMA Configuration	NEMA 5-15
NEMA Rating	Rain Tight
Product Name	Safety Yellow
Type	String Lights
UPC	78678840869

Agency

UL	E112216
----	---------

Electrical

Lamp Wattage - Maximum	200W
Lumens	2000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Incandescent
Cord Length - Primary	2.43m (8.0')
Cord Length - Secondary	0.61m (2.0')
Cord Type - Primary	12/3 SJTW
Depth	N/A
Duty	Commercial
Guard Included	No
Guard Type	N/A
Height	N/A
Lamp Type	A21

Length	30.48m (100.0')
Material - Guard	N/A
Mounting Style	Stringer
Net Weight	2.700/kg
Outlet	None
Packaging Type	Carton
Socket Construction	Molded

This document was generated on Sep 13, 2025