

2-RowStraight Plated Thru Hole PCB Connector with Mounting Ears (PLUG)

RM21, PCB Plated Thru Hole, Straight Plug with mounting ears, 2-Row, Sizes: 10-100 | R Series

A family of male PCB mounted connectors that have two rows of contacts spaced at 0.075". These connectors have a vertical mounting orientation and mount to plated thru holes of the PCB. These connectors have mounting ears to secure the connector to the board. They are available in sizes ranging from 10 to 100 contacts.

DOCUMENTS | SPECIFICATIONS | ADDITIONAL INFO

- Dimensional Information »
- Part Number Buildup »
- PC Board Layout »
- Fortron Discoloration »
- Contact Spring Plating »
- View More »

PRODUCT MATES WITH

Image Coming Soon — 2 Row Crimp Removable Cable Connector with Mounting Ears (RECEPTACLE) »

 2 Row Crimp Removable Cable Connector without Mounting Ears (RECEPTACLE) »

 2 Row Crimped Wire Cable Connector with Mounting Ears (RECEPTACLE) »

 2 Row Crimped Wire Cable Connector without Mounting Ears (RECEPTACLE) »

VIEW MORE »

Build a Part Number

RM	2	1	2	-	040	-	10	2	-	55	00	
1 SERIES DESIGNATOR	2 BODY ROWS	3 BODY STYLE	4 BODY MATERIAL		5 SIZE		6 CONTACT TYPES	7 CONTACT PLATING		8 HARDWARE STYLE	9 POLARIZATION	10 OPTIONS

TO BEGIN: SELECT COMPONENTS

1 SERIES DESIGNATOR — RM - .075" Screw Machine PC Connector

2 BODY ROWS — 2 - Row

1 - Plug, Straight, With Mounting Ears

To take action, please complete the steps to the left.

NEXT STEPS: TAKE ACTION

Part #:

Miltary #:

- Quote
- Mechanical Model & Drawing
- Product Sample

REQUEST NOW

VIEW INVENTORY

Find a Sales Rep

Looking to talk with a salesperson? Find your local representative here:

Downloaded from Arrow.com.

STYLE

4 BODY MATERIAL

- 2 - Polyphenylene Sulfide (PPS)

5 SIZE

- 10 Contacts
- 20 Contacts
- 30 Contacts
- 40 Contacts
- 50 Contacts
- 60 Contacts
- 70 Contacts
- 80 Contacts
- 90 Contacts
- 100 Contacts

6 CONTACT TYPES

- 10 - Pin, Straight, Dip Solder, .109" x .020" dia
- 12 - Pin, Straight, Dip Solder, .140" x .020" dia
- 13 - Pin, Straight, Dip Solder, .172" x .020" dia
- 14 - Pin, Straight, Dip Solder, .250" x .020" dia

7 CONTACT PLATING

- 1 - Gold Plated Termination
- 2 - Pre-Tinned Termination, SnPb Alloy
- 3 - Pre-Tinned Termination, SAC305 Alloy

8 HARDWARE STYLE

55 - Guide Set

9 POLARIZATION

00 - None (Polarization is not required or pol

10 OPTIONS (OPTIONAL)

LOCATIONS

CONTACT US

Customize Your Solution

AirBorn will work with you to design and build a product to your specifications.

LEARN MORE

Downloaded from Arrow.com.

© 2015 AirBorn, Inc. All Rights Reserved.

100% Employee Owned

ISO9001 and AS9100 Certified

DDTC Registered - Expiration 7/31/2017

Website Design and Development by BoxCrush®

Downloaded from Arrow.com.