



Part Number : [39000091](#)

Product Description : Mini-Fit Female Crimp Terminal, Gold (Au) over Brass, 28-22 AWG, Reel

Series Number : 5556

Status : Active

Product Category : Crimp Terminals

Engineering Part Number : 5556GS5



Documents and Resources

Drawings

[039000091_sd.pdf](#)

[55560001-PK-000.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[55560001-AS-000.pdf](#)

[55560002-AS-000.pdf](#)

[55560002-PS-CH-000.pdf](#)

[55560002-PS-ES-000.pdf](#)

[55560002-PS-SK-000.pdf](#)

[55560008-TS-000.pdf](#)

[PS-5556-001-001.pdf](#)

[PS-5556-002-001.pdf](#)

[PS-5556-003-001.pdf](#)

[55560001-TS-000.pdf](#)


[55560010-TS-000.pdf](#)

[TS-5556-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 33; 44;
------------	----------------------------------

	34
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	5556
Description	Mini-Fit Female Crimp Terminal, Gold (Au) over Brass, 28-22 AWG, Reel
Application	Wire-to-Board, Wire-to-Wire
Product Name	Mini-Fit
UPC	822348427017

Electrical

Current - Maximum per Contact	9.0A
-------------------------------	------

Voltage - Maximum	600V
-------------------	------

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.130/g
Packaging Type	Reel
Plating min - Mating	0.381µm
Plating min - Termination	0.381µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.80-3.10mm
Wire Size (AWG)	22, 24, 26, 28
Wire Size mm ²	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
Mini-Fit Jr. Receptacle Housings	5557
Mini-Fit BMI Dual Row Receptacle Housings	44516
Mini-Fit BMI Dual Row Receptacle Housings	42474
Mini-Fit BMI Dual Row Receptacle Housings	43760

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Mini-Fit Jr. Male and Female	638191000

Terminals, 28-22 AWG	
FineAdjust Applicator for Insulation Diameter 1.30-1.50mm, 28-22 AWG Wire	<u>639002700</u>
FineAdjust Applicator for Insulation OD 1.10-1.30mm - 28-22 AWG	<u>639020200</u>
FineAdjust Applicator for Insulation OD 0.95-1.08mm - 28-22 AWG	<u>639023800</u>
T2 Terminator for Insulation OD 1.30-1.50mm, 28-22 AWG	<u>639102700</u>
T2 Terminator for insulation OD 1.10-1.30mm - 28-22 AWG	<u>639120200</u>
T2 Terminator for Insulation Diameter 0.95-1.08mm, 28-22 AWG	<u>639123800</u>

This document was generated on Jun 02, 2026