



Quality Products. Service Excellence.

Low-Profile Wall Mount Cabinet *HLP Series*

Rated 200 lbs Weight Capacity



It's official! We've completely redesigned the HLP, reducing the cost and improving the features! The HLP is perfect for your networking and server installations, in tight spaces.

Features

- Available in two (2) heights up to 41 inches of usable space, and three (3) fixed rack unit options.
- Each cabinet ships with a 2U pivoting rack rail and a fixed rack rails of your choosing.
 - Optional pivoting 180 degrees rails available for even easier equipment mounting.
 - Rails install in three positions, providing 180 degrees of equipment mounting options.
 - Fixed rack mounting units available in 4U, 6U and 8U.
- Locking hinged front door includes side venting for airflow.
 - Door and latch can be reversed to swing left-to-right.
- Rear wall mounting section features 3.00", 2.00", 1.38" and 1.12" conduit knockouts on top and bottom.
- Side venting are designed for optional fans for active cooling.
- Generous cable management lances located on the rear section.
- Heavy duty keyhole for wall mounting.
- Large knockouts in rear for cable access.

Specifications

- Body and rear section constructed of 16-gauge steel.
- Rack rails are 14-gauge steel with 10-32 tapped EIA mounting rails.
- Dedicated bonding points that also provide drill-less mounting of electrical 4x2 utility boxes.
 - Grounding kit sold separately - **GRDKIT01** or **GRDKIT04**.
- Rated for up to 200 lbs (91 kg) static load rating.
- Body and door are finished in rugged sand-textured black powder paint. The rack rails are finished in smooth white powder paint.
 - Available in White and Light Gray (special order).
- TAA Compliant.
- RoHS Compliant.
- Manufactured in North America.

Gallery



Accessories

- Cabinet Fan Kits
- Ground Wire Kits
- Hook and Loop Roll

- 10-32 Mounting Screw and Clip Nut Combo-Pack
- Two Post Mounting Clamping Shelf
- Outlet Strips
- Universal Rack Shelf

New Design

Part No.	Overall Dimensions			Rack Units	Maximum Vertical Usable Depth
	Height	Width	Depth		
HLP4U31BK	31.00	27.50	11.15	4U	29.00
HLP4U43BK	43.00	27.50	11.15	4U	41.00
HLP6U31BK	31.00	27.50	15.46	6U	29.00
HLP6U43BK	43.00	27.50	15.46	6U	41.00
HLP8U31BK	31.00	27.50	19.65	8U	29.00
HLP8U43BK	43.00	27.50	19.65	8U	41.00

Old Design (Available While Supplies Last)

Part No.	Overall Dimensions			Rack Units	Horizontal Usable Depth	Vertical Usable Depth	Replaced by Part No.
	Height	Width	Depth				
HLP4UBK	31.00	27.50	10.80	4U	7.00	29.00	HLP4U31BK
HLP6UBK	31.00	27.50	15.05	6U	10.50	29.00	HLP6U31BK
HLP8UBK	31.00	27.50	19.30	8U	14.00	29.00	HLP8U31BK

Optional 180-Degree Rotating Mounting Rail Kits

Part No.	Mounting Dimensions		Rack Units	Rotation
	Height	Width		
HLP2UR	3.50	19.00	2U	180 Degrees
HLP4UR	7.00	19.00	4U	180 Degrees
HLP6UR	10.50	19.00	6U	180 Degrees
HLP8UR	14.00	19.00	8U	180 Degrees

Data subject to change without notice

© 2018. Hammond Manufacturing Ltd. All rights reserved.