

Specification Sheet

Part Number: 126-00042

Easy and quick insertion ideal for production environment.

Tie "clicks" into place upon final installation signaling installer insertion is complete.

Arrowhead style mount provides low insertion and high extraction force.



1-Piece Cable Tie with Arrowhead Mount with Wings, 4.5"L, 18lb, 0.19 - 0.22" Mtg Hole, PA66HS, Black, 1000/pkg

Article Number	126-00042
----------------	-----------

Type	T18RWPM
------	---------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Wing design helps stabilize the tie in high vibration applications. One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.
---------------------	--

Short Description	1-Piece Cable Tie with Arrowhead Mount with Wings, 4.5"L, 18lb, 0.19 - 0.22" Mtg Hole, PA66HS, Black, 1000/pkg
-------------------	--

Global Part Name	T18RWPM-PA66HS-BK
------------------	-------------------

Minimum Tensile Strength (Imperial)	18
-------------------------------------	----

Minimum Tensile Strength (Metric)	80
-----------------------------------	----

Length L (Imperial)	4.5
---------------------	-----

Length L (Metric)	113.0
-------------------	-------

Fixation Method	Arrowhead
-----------------	-----------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.1
--------------------	-----

Width W (Metric)	2.5
------------------	-----

Bundle Diameter Min (Imperial)	0.06
--------------------------------	------

Bundle Diameter Min (Metric)	1.5
------------------------------	-----

Bundle Diameter Max (Imperial)	0.87
--------------------------------	------

Bundle Diameter Max (Metric)	22.0
------------------------------	------

Thickness T (Imperial)	0.043
Thickness T (Metric)	1.1
Height H (Imperial)	.23
Height H (Metric)	5.80
Panel Thickness Min (Imperial)	0.06
Panel Thickness Max (Imperial)	0.13
Panel Thickness Min (Metric)	1.52
Panel Thickness Max (Metric)	3.2
Mounting Hole Diameter D (Imperial)	0.19 - 0.22 "
Mounting Hole Diameter D (Metric)	4.8 - 5.6 mm
Mounting Hole Diameter D Min (Imperial)	0.19
Mounting Hole Diameter D Max (Imperial)	0.22
Mounting Hole Diameter D Max (Metric)	5.6
Disc Diameter (Metric)	13.2
Disc Diameter (Imperial)	0.5

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)