





REV.	DATE	DESCRIPTION
A	01/13/99	ADD CRIMP NOTES / CHANGE FERRULE DIMS.



RECOMMENDED CABLE
STRIPPING DIMENSIONS



NOTE:
USE .151 HEX CRIMP DIE TO
TERMINATE FERRULE TO CABLE.
- CONNEX TOOL 47-10160
- IDEAL TOOL 36-489

	DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS	APPROVALS	DATE	 Connector Corporation				
1	HOUSING	BRASS	NICKEL	DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5--6 = ± 0.2 6--30 = ± 0.4 30--120 = ± 0.6 120--315 = ± 1 315--1000 = ± 1.6 1000--2000 = ± 2.4	DRAWN	G.R.S.	01/13/99	TITLE MCX STRAIGHT CRIMP PLUG (FOR RG 316 DOUBLE BRAID)			
2	BODY	BER. COPPER	NICKEL		CHECKED						
3	INSULATOR	TEFLON	NATURAL		ISSUED						
4	INSULATOR	TEFLON	NATURAL					SIZE	FSCM NO.	DWG. NO.	REV.
5	CONTACT PIN	BRASS	GOLD 30 MIN.				A	99001	252120.DWG	A	
6	FERRULE	COPPER	NICKEL								
7											
8				DO NOT SCALE DRAWING			SCALE	NA	PART NO.	SHEET	
								252120		1 OF 1	