

 [PRODUCTS](#) ▾

 [DISTRIBUTOR INVENTORY](#)

 [INDUSTRIES](#) ▾

 [SUPPORT](#) ▾

 [NEWS & EVENTS](#) ▾

 [ABOUT US](#) ▾

12TW1-1M

[Products](#) > [Switches](#) > [Toggle Switches](#) > [TW Series](#) > [12TW1-1M](#)

Overview

MICRO SWITCH TW Series Toggle Switch, 2 pole, 3 position, Solder terminal, Locking Lever, Military Part Number MS27721-21-1M....

[View More](#)



 [view all 12TW1-1M literature](#)

 [view distributor inventory](#)

 [sample request](#)

 [email support](#)


 [get support](#)

 [email sales](#)

 [find a distributor](#)

 [email this page](#)

Technical Specifications

Series Name	TW	Product Type	MICRO SWITCH Toggle Switch
Ampere/Voltage Range (Resistive Load)	0.1 A to 5.0 A at 0.5 Vac to 115 Vac 0.1 A to 5.0 A at 0.5 Vdc to 28 Vdc	Circuitry	DPDT
Action	3 position	Circuitry/Operating action	
Mounting	Bushing 15/32 in	Termination	Solder
MIL Spec. Number	MS27721-21-1M	Lever Type	Locking

[View More](#)

View documents in: [English](#) ▾

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
 12TW1-1M highres photo	Photo	English	3MB
 MICRO SWITCH TW Series Miniature Military-Grade Toggle Switches	Datasheet	English	1MB
 12TW1-1M lowres photo	Photo	English	253KB
 Sensors and Switches in Oil Rig Applications	Application Note	English	7MB

[View More](#)

Product Features

- Qualified to MIL-DTL-83731
- Save space and weight
- SPDT and DPDT circuitry
- Temperature range: -65 °C to 71 °C [-85 °F to 160 °F]
- Sealed bushing versions
- Choice of 1/4 in or 15/32 in bushing
- Color tab available on 15/32 in. bushing
- UL recognized

Applications

- Industrial machinery and equipment
- Military and commercial aviation
- Construction equipment
- Test instruments
- Agricultural machinery
- Process control
- Medical instrumentation

NAVIGATION LINKS

[HOME PAGE](#)

[PRODUCTS](#)

[DISTRIBUTOR INVENTORY](#)

[INDUSTRIES](#)

[SUPPORT](#)

[NEWS & EVENTS](#)

[ABOUT US](#)

DISTRIBUTOR LINKS

[ECOM LOGIN](#)

[LEARN CENTER](#)

[REQUEST ACCESS TO ECOM](#)

[SALES/AD PORTAL LOGIN](#)

[SALES/AD PORTAL ACCESS REQUEST](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

LANGUAGE

[English](#) 

SOCIAL MEDIA



SITE INFORMATION

[PRIVACY STATEMENT](#)

[SITEMAP](#)

[TERMS & CONDITIONS](#)

COPYRIGHT © 2018 HONEYWELL
INTERNATIONAL INC.