Specification Sheet

Part Number: SNP33GHS0H4



Installation and removal can be five times faster than conventional clamps.

Completely reusable.

Will not rust or corrode.

Safety engineered.

No protruding band or cluster.

Can be installed with hose in place.

One-hand installation for tight places.

Snapper Hose Clamp, 1.29 - 1.59" Bundle Diameter, PA66GF13, Black, 500/pkg

Article Number	190-00148
Type	SNP33
Color	Black (BK)
Quantity Per	pack

Downloaded from Arrow.com.

Product Description	The Snapper Hose Clamp features a ratchet-style closure for reduced assembly time. It can be added after connection of the hose. Release by sliding the ratchet ends apart. Snappers can be used in under-hood applications and are stable in a wide variety of chemicals including salts, bases, alcohols, ethers, detergents, gasoline, lubricating oils and greases. They are manufactured in black PA66 glass filled, impact modified, heat stabilized material. Custom design and color options are available based upon application and volume requirements.
Short Description	Snapper Hose Clamp, 1.29 - 1.59" Bundle Diameter, PA66GF13, Black, 500/pkg
Global Part Name	SNP33-PA66GF13-BK
Fixation Method	Plug-in mounting
Variant	Closed
Bundle Diameter Min (Imperial)	1.29
Bundle Diameter Min (Metric)	32.8
Bundle Diameter Max (Imperial)	1.59
Bundle Diameter Max (Metric)	40.4
Wall Thickness WT (Imperial)	.068
Wall Thickness WT (Metric)	1.717
Material	Polyamide 6.6 glass filled impact modified heat stabilized (PA66GF13)

Downloaded from Arrow.com.

Material Shortcut	PA66GF13
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes

Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

Downloaded from Arrow.com.