Part Number : 1069200000
Product Description : Optical Splice Protection Sleeve, Single Fiber, Outer Tube Outer Diameter 2.30mm and Length 40.00mm (After Shrinkage)
Series Number : 86290
Status : Active
Product Category : Optical Fibers



Documents and Resources

Drawings

1069200000_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Active
Category	Optical Fibers
Series	86290
Description	Optical Splice Protection Sleeve, Single Fiber, Outer Tube Outer Diameter 2.30mm and Length 40.00mm (After Shrinkage)
Application	Fiber Closure Installation, Field Fiber Splicing Assembly, Manufacturing, Network Infrastructure
Product Name	Optical Splice Protection
UPC	196823222108

Physical

Cable Length	40.00mm
Color - Cable Jacket	Clear
Internal Diameter	1.50mm
Material - Outer Jacket	Polyolefin
Outer Diameter	2.30mm
Packaging Type	Bag
Temperature Range - Operating	-55° to +105°C
Wire/Cable Type	N/A

Downloaded from Arrow.com.