




Part Number : [1300380016](#)
Product Description : DeviceNet Mount, 14 Ports, no LEDs, with Mini-Change 5 Pole Home Run Connector
Series Number : 130038
Status : Not Recommended For New Design
Product Category : Passive Distribution Boxes
Engineering Number : DNTA14114A1



Documents & Resources

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS |  |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Not Reviewed per D(2024)7663-DC (21 Jan 2025) |
| EU RoHS | Not Compliant per EU 2015/863 |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

| | |
|--------------|--|
| Status | Not Recommended For New Design |
| Category | Passive Distribution Boxes |
| Series | 130038 |
| Description | DeviceNet Mount, 14 Ports, no LEDs, with Mini-Change 5 Pole Home Run Connector |
| IP Rating | IP67 |
| Product Name | DeviceNet,Nano-Change (M8) |
| UPC | 78678872749 |

Electrical

| | |
|-------------------------------|----------|
| Current - Maximum per Contact | 1.68A |
| Functional Wiring | Parallel |
| Voltage - Maximum | 36V DC |
| Wiring Configuration | N/A |

Physical

| | |
|-------------------------------|----------------------|
| Bus I/O | Nano-Change (M8) |
| Cable Connector Orientation | N/A |
| Home Run Cable Length | N/A |
| Home Run Connector | Mini-Change - 5 pole |
| Home Run Interface | Integrated Connector |
| Keyway | N/A |
| LED Indicator | None |
| Material - Cable Jacket | N/A |
| Material - Housing | ABS |
| Net Weight | 1.000/g |
| Orientation | Top-Mount |
| Poles | 5 |
| Poles (wired) | 5 |
| Ports | 14 |
| Temperature Range - Operating | 0°C to +60°C |

This document was generated on Apr 22, 2025