



RHYTHM: (UL) E88231 SJT 3X14AWG(2.08mm²)
105°C 300V VW-1 CSA LL54496 SJT
3X14AWG(2.08mm²)105°C 300V VW-1
RHYTHM R

1. PLUG : LT-602 AMERICAN TYPE
2. CONNECTOR : LT-501 IEC-320 C13
3. CORD : SJT 14AWGX3C 105°C BLACK 1.5M
4. APPROVALS : UL, C-UL
5. Supplier for flexible cord : RHYTHM
6. Hi-Pot Test: 2000v/1min<1mA>

	DESCRIPTION	DATE

DRAWER	Eric	DATE	20/10/24	P/N	800-1400-2-SJT0-BL-00150-1
APPROVE		REV.	0	Dr.No.	1091098
		比 例		TOL.	±5mm
				ALL DIMENSIONS IN mm	

CnC Tech

Industrial Cable and Connector Technology