



Part Number : [2188760064](#)
Product Description : 5G mmWave RF Flex-to-Board Receptacle, 0.35mm Pitch, 0.70mm Mated Height, Series 5G25, 2 Reels/Carton
Series Number : 218876
Status : Active
Product Category : Board-to-Board Connectors



Documents & Resources

Drawings
[2188760064_sd.pdf](#)

3D Models and Design Files
[2188760064.dxf](#)
[2188760064.pdf](#)
[2188760064_stp.zip](#)

Specifications
[2188760000-AS-000.pdf](#)
[2188769200-SPK-201.pdf](#)
[2188760000-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	218876
Description	5G mmWave RF Flex-to-Board Receptacle, 0.35mm Pitch, 0.70mm Mated Height, Series 5G25, 2 Reels/Carton
Series Name	0.35, 5G25
Application	Board-to-Board
Component Type	PCB Receptacle
Product Name	5G mmWave
UPC	196823288982

Electrical

Current - Maximum per Contact	0.3A, 1.0A
Voltage - Maximum	50V AC (RMS)/DC

Physical

Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black
Durability (mating cycles max)	10
Glow-Wire Capable	No
Mated Height	0.70mm
Mated Width	2.76mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold

Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	10.483/mg
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	Yes
Pitch - Mating Interface	0.35mm
Pitch - Termination Interface	0.35mm
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
5G mmWave RF Flex-to-Board Plug, 0.35mm Pitch, 0.70mm Mated Height, Series 5G25, 2 Reels/Carton	<u>2188770064</u>

This document was generated on Apr 26, 2025