


△ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



STUD SIZE		INSULATION DIA				
製品番号	スタッドサイズ	Hφ	被覆外径 D	L1	L2	D
171508-1	#6	3.68	2.03~3.18	20.3	16.7	7.1
-2	#8	4.34	2.03~3.18	20.3	16.7	7.1
-3	#10	5	2.03~3.18			
-4	#6	3.68	2.67~3.56	20.3	16.7	7.1
-5	#8	4.34	2.67~3.56	20.3	16.7	7.1
-6	#10	5	2.67~3.56			
-7	5mm	5.26	2.03~3.18			
-8	5mm	⑤ 5.2	2.67~3.56	21.4	17.5	7.9
171508-9	#4	3.02	2.03~3.18			

OBSOLETE

OBSOLETE

OBSOLETE

OBSOLETE

K	REVISED PER ECR-17-018225	Y.O	E.T	27DEC17	参考図面 (CUSTOMER COPY REFERENCE ONLY)			
J	REVISED PER ECR-17-007066	T.G	N.Y	26MAY17	材料 MATERIAL: 電線銅 COPPER		TE Connectivity	
H	OBSOLETE	Y.O	N.Y	14APR17	H: FINISH ANNEAL TIN PL 焼付め 銅めっき			
G	Change Applicable Body	Y.O	N.Y	23JAN17	絶縁体 INSULATION DIA 0.26~1.04 mm (AWG 22-16)		分組 CLASS	
F2	REVISED PER ECO-11-005030	RK	HMR	23MAR11	規格仕様 INSULATION DIA 0.26~1.04 mm (AWG 22-16)		形式 TYPE P.I.D.G	
LTR	変更 REVISION RECORD	DR	CHK	DATE	公差 TOLERANCE EXCEPT AS NOTED ±0.4 ±1.0		LOF SIZE 4-1	
DR	2/6/13	DE	2/6/13		J A C-171508		REV K	
CHK	1/10/13	APP	1/10/13		丸型端子 WIRE TERMINAL ASSEMBLY			

C-171508

単位: 寸法 DIMENSIONS IN MM DO NOT SCALE PRINT