

D					
C	Wire _____ Cu tin plated				
	Gauge stranded _____ AWG 30 / 7 strands AWG 38				
	Voltage rating _____ 150 V				
	Capacitance _____ 83,2 pF/m (single end)				
B	_____ 47,6 pF/m (differential)				
	Impedance _____ 67 Ω (single end)				
	_____ 110 Ω (differential)				
	Conductor resistance _____ 348 mΩ/m				
A	Signal delay _____ 5,31 ns/m				
	Insulation material _____ PVC				
	Temperature rating _____ -30°C to +105°C				

				Dat.	Name		Flat cable Length per reel : 30,48 m 68 poles, UL 2678	Maßstab/ Scale 6:1
			Detail.	31/05/07	PK			
			Insp.					
			Stand.					
							TB 60 90 068 6008	Blatt/ Page 1 / 1
34361	31/05/07	PK	HARTING EURL F-95972 Paris					
Mod.	Dat.	Name						