




PRODUCT NUMBER	PITCH
HWxx30x200J0G	3.81 mm



Material:

- Item ① Top body: Thermoplastic (UL94V-0)
- Item ② Bottom body: Thermoplastic (UL94V-0)
- Item ③ Terminal lever: Thermoplastic (UL94V-0) Orange(RAL2011/P)
- Item ④ Spring clamp: Stainless Steel
- Item ⑤ Female contact: PhBz (CuSn) Tin plated
- Item ⑥ Flange screw: Steel M2.5 plated zinc * +/- * combination type

Electrical

- Voltage rating: 300V
- Current rating: 8A
- Solid wire(AWG): 16-28
- Stranded wire(AWG): 16-28
- Wire strip length: 8-9mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval:

N=Number of poles
Dim A=Nx3.81+0.80
Dim B=(N-1)x3.81
Dim C=(N-1)x3.81+9.0
Dim D=(N-1)x3.81+14.4

Poles	Tolerance
2P-6P	±0.10
7P-12P	±0.20
13P-18P	±0.30
19P-24P	±0.40

PART NO.: HW xx 3 0 x 2 00J 0 G

Solid block	0	Black (RAL9005)	RoHS compliant (lead<4%) In copper Alloy
No. of poles	2	Red (RAL3001/D)	
02	2 poles	3	Orange(RAL2011/P)
03	3 poles	4	Yellow(RAL1018/A)
...	...	5	Green(RAL6018/T)
24	24 poles	6	Blue (RAL5015/A)
		8	Grey(RAL7035/D)
		9	White(RAL1102)
		C	Green(RAL6018/U)

mat'l. code		surface ASME Y14.5	tolerance ASME Y14.5	projection	product family
ltr	ecn no	dr	date		TERMINAL BLOCK
tolerances unless otherwise specified				MM	title
angles	0	X.±0.5		scale	TERMINAL BLOCK
0	X.X±0.3				SPRING CLAMP, PLUGGABLE PLUG, WITH FLANGE
X*±1"		X.XX±0.1		dwg no	sheet 1 of 1 size
dr	EVIN ZHONG	051514		HWxx30x200J0G	A4
enr	EVIN ZHONG	051514		type	CUSTOMER Drawing
chr	HANKE FENG	051514			
appd	SHI JUN	051514			
sheet index	revision sheet	A	1		