


PropacPRO Front Hood, Bottom Hinged, 3 U, 84 HP

CATALOG NUMBER

24576-083



The front hood bottom hinged can be assembled on to a PropacPRO case. It protects the PCB from accidental operations. A retrofittable lock can be installed.

CERTIFICATIONS



FEATURES

Mounting of hinges at top or bottom

Lock (max. 2) retrofittable

From acrylic glass, hinged, removable

Lateral cover (item 5) also serves as vertical EMC shielding of side panels

PRODUCT ATTRIBUTES

Rack Width: 84HP

Package Quantity: 1

Material: Thermoplastic

Product Family: PropacPRO

Product Type: Cover Plate

Rack Height: 3U

Type: Front Hood

Works With: Cases

ADDITIONAL PRODUCT DETAILS

Cannot be combined with design elements.

Other heights available on request.

Before assembly of hood feet must be fixed to case; please order separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE