Rack Mount Basic PDU *1582E DP Series*

10A Double Pole | Single-Phase 100-240V | Front or Rear Facing C13 Outlets







Features

- On-Off switch is rocker type (double pole, single throw) with green light.
- Rated 100-240VAC (TUV), 120-240VAC (UL), 10A, 50/60Hz
- Designed for power distribution on front or rear of unit with IEC power cords.
- 1U horizontal 19" rackmount installation.
- All steel housing with black powder coat. Complies with the Greenguard guidelines for indoor air quality.

Specifications

- Includes 10A circuit breakers to prevent accidental line overload.
- cULus Listed UL 62368-1 (2nd Edition), 2014-12-01, and CAN/CSA C22.2 No. 62368-1-14 (2nd Edition).
- TÜV-SUD Certified to EN 62368-1:2020/A11:2020, and IEC 62368-1:2018.
- TÜV-SUD tested for EMC Compliance to EN 55032:2015+A11:2020 (CISPR 32:2015+A1:2019) & EN 55035:2017+A11:2020 (CISPR 35:2016).
- CE compliant to the European Low Voltage Directive 2014/35/EU.
- CE compliant to the European EMC Directive 2014/30/EU.
- UKCA compliant to British Electrical Equipment (Safety) Regulations 2016 (S.I. 2016/1101).
- UKCA compliant to British Electromagnetic Compatibility Regulations 2016 (S.I. 2016/1091).
- TAA-compliant for federal GSA schedule purchases within the USA.
- RoHS Compliant.
- Manufactured in North America.

Accessories

- Hardware for Rack Mounting Solutions
- Rail Depth Adapter Kit
- Power Cords

Downloaded from Arrow.com.

With Illuminated On/Off Switch Part No.	Overall Dimensions Height	Width	Depth	Number of Outlets Front	Rear	Outlet Type	Inlet Type	Inlet Location
1582H8E1BKDP	1.72	19.00	2.66	8	0	C13	C14	Rear
1583H8E1BKDP	1.72	19.00	2.66	0	8	C13	C14	Rear

Tags: **IEC**

Data subject to change without notice.

© 2026. Hammond Manufacturing Ltd. All rights reserved.

Downloaded from Arrow.com.