



## HSG150T48PF, Heat Shrink Tubing, Thin Wall, Green

By Burndy  
Catalog # [HSG150T48PF](#)

1.5" ID Min (Expanded), .75" ID Max (Recovered), Thin Wall, Green, 4-Foot Reel



### Features

- Heat Shrink Tubing
- 1.5" ID Min (Exp), .75" ID Max (Rec)
- 2/0-350, Polyolefin, Thin Wall, Green
- Shrink Ratio 2:1
- 4 Foot Reel

### Specifications

|                                    |     |
|------------------------------------|-----|
| Certification - CSA Approved       | Yes |
| UL Listed                          | No  |
| Certification - ETL                | No  |
| Standards - RoHS Compliance Status | CM  |

### Conductor

|                 |                      |
|-----------------|----------------------|
| Conductor Range | #2/0 AWG - 350 Kcmil |
| Conductor Size  | 250kcmil - 500kcmil  |

### Configuration

Connector Type THIN WALL REEL

### Dimensions

|            |                         |
|------------|-------------------------|
| Width      | 1.5 in                  |
| Height     | 1.5 in                  |
| Length     | 48 in                   |
| Dimensions | 48 in x 1.5 in x 1.5 in |

### General

|          |                         |
|----------|-------------------------|
| Material | Cross-linked Polyolefin |
| UPC      | 781810212998            |
| Color    | Green                   |

### Logistics

Minimum Pack Quantity 1

### Product Assets

[Catalog \[English\]](#)

