

 PRODUCTS ▾

 DISTRIBUTOR INVENTORY

 INDUSTRIES ▾

 SUPPORT ▾

 NEWS & EVENTS ▾

 ABOUT US ▾

2450RG 86930002

Products > Sensors > Humidity, Thermal & Flexible Heater Products > Thermostats/Thermal Switches > Commercial > Automatic Reset > 2450RG Series > **2450RG 86930002**

Overview

2450RG Series Phenolic Automatic Reset Thermostats.

The 2450RG Series consists of a temperature-sensitive bimetal disc, electrically isolated from the switch, which actuates the

[View More](#)



 view all 2450RG 86930002 literature

 view distributor inventory

 sample request

 email support

 get support

 email sales

 find a distributor

 email this page

Technical Specifications

Functional Properties	Open on rise	Reset Type	Automatic
Operating Temperature	0 °C to 150 °C [32 °F to 302 °F]	Amperage	0.5 A
Voltage	250 Vac/50 Vdc	Open Temperature	110.0 °C [230 °F]
Open Tolerance	3.9 °C [7 °F]	Close Temperature	87.8 °C [190 °F]
Close Tolerance	6.2 °C [11 °F]	Environmental Exposure Range	-18 °C to 177 °C [0 °F to 350 °F]

[View More](#)

View documents in: 

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
 Commercial Thermostats	Datasheet	English	756KB
 Thermostats Line Guide	Product Line Guide	English	444KB
 Thermal Sensors	Product Range Guide	English	2MB

Product Features

- Cost effective
- Rivet sleeve construction
- Low profile
- Logic level contacts

Applications

- HVAC
- Automotive
- Office copy machines
- Heat and smoke detectors
- Major appliances

[HOME PAGE](#)[PRODUCTS](#)[DISTRIBUTOR INVENTORY](#)[INDUSTRIES](#)[SUPPORT](#)[NEWS & EVENTS](#)[ABOUT US](#)[ECOM LOGIN](#)[LEARN CENTER](#)[REQUEST ACCESS TO ECOM](#)[SALES/AD PORTAL LOGIN](#)[SALES/AD PORTAL ACCESS REQUEST](#)[SAMPLE REQUEST](#)[SUPPLIER MICROSITE](#)[English](#)[SOCIAL MEDIA](#)[SITE INFORMATION](#)[PRIVACY STATEMENT](#)[SITEMAP](#)[TERMS & CONDITIONS](#)

COPYRIGHT © 2018 HONEYWELL
INTERNATIONAL INC.