

SEK CAB FLAT COLOR AWG28/7 28P 30,48m



Image is for illustration purposes only. Please refer to product description.

Part number	09 18 028 7005
Specification	SEK CAB FLAT COLOR AWG28/7 28P 30,48m
HARTING eCatalogue	https://b2b.harting.com/09180287005

Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (flat)

Version

Cable length	30.48 m
Number of cores	28
Core structure	AWG 28/7

Technical characteristics

Limiting temperature	-30 ... +105 °C unmoved -20 ... +105 °C moved
Impedance	100 Ω
Conductor resistance @ 20 °C	$\leq 216 \Omega/\text{km}$
Insulation resistance @ 20 °C	$\geq 20 \text{ M}\Omega \times \text{km}$

Material properties

Material (cable)	PVC
Colour (cable)	Colour coded
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Commercial data

Packaging size	1
Net weight	1,844 g
Net weight	52 g/m
Country of origin	USA
European customs tariff number	85444993
GTIN	5713140024984
eCl@ss	27061801 Data and communication cable (copper)