

**Part Number :** [1731090285](#)

**Product Description :** FCT Standard-Density D-Sub Connector, Female, Straight, PCB Through Hole, 17.10mm Tail Length, Gold Plating, 500 Mating Cycles, 14.20mm Snap-in Bolt, 25 Circuits, White Insulator

**Series Number :** 173109

**Status :** Active

**Product Category :** D-Sub Connectors

**Engineering Number :** F25S80G1-1254



---

## Documents & Resources

### Drawings

[1731090285\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2021)10043-DC (17 Jan 2022)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	D-Sub Connectors
Series	173109
Description	FCT Standard-Density D-Sub Connector, Female, Straight, PCB Through Hole, 17.10mm Tail Length, Gold Plating, 500 Mating Cycles, 14.20mm Snap-in Bolt, 25 Circuits, White Insulator
IP Rating	IP20
Magnetic	Yes
Product Name	FCT Products
Type	Standard Density
UPC	889056761369

### Electrical

Current - Maximum per Contact	7.5A
Shielded	Yes

### Physical

Circuits (Loaded)	25
Circuits (maximum)	25
Color - Resin	White

Durability (mating cycles min)	500
Gender	Female
Material - Contact	Copper Alloy
Material - Resin	PBT
Material - Shell	Steel
Net Weight	16.600/g
Number of Rows	2
Orientation	Straight
Packaging Type	Carton
Panel Mount	Rear
Panel Mount Method	Thread-In
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
PC Tail Length	17.10mm
Pitch - Mating Interface	2.84mm
Pitch - Termination Interface	2.84mm
Plating - Contact	Gold over Nickel
Plating - Shell	Tin
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-55° to +125°C
Termination Style	Through Hole
Waterproof / Dustproof	No
Waterproof / Dustproof Type	IP20

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Mates With	FCT Standard-Density D-Sub, Size 3, 25 Position, Plug

---

This document was generated on Sep 10, 2025