


© 2021 TE Connectivity. All Rights Reserved.

CENTER CONTACT 2327554-1, RTK031
Innenleiter Kontakt 2327554-1, RTK031


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL RELEASE	28OCT2021	SA	CS
	C	INCREASED CONTACT LAMELLA	15SEP2023	SA	CS







SECTION B-B
20:1




NOTES


1. PACKAGING: PRODUCT REELED ON CORRUGATED REEL WITH INTERLEAVING PAPER
   Verpackung: Spulenware auf Wellpappespule mit Zwischenlagenpapier

△2 WEIGHT INCLUDING CARRIER STRIP
Gewicht mit Trägerstreifen

△3 MICROSECTION FOR CRIMP INSPECTION HAVE TO BE DONE ON SHOWN POSITION
Schliffbild zur Crimpüberwachung ist bei angezeigter Position durchzuführen

△4 UNSEALED APPLICATION/ Ungedichtete Applikation 114-94566
SEALED APPLICATION/ Gedichtete Applikation 114-94705





C	A	WEIGHT [g]	CABLE TYPE	WIRE RANGE	SURFACE	MATERIAL	REV	PART NO.
1.5	1.7	0.061	RG174	0.14mm^2	Sn	CuSn	C	2327554-2
1.53	1.8	0.047	RTK031	0.35mm^2	Sn	CuSn	C	2327554-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±0.2
1 PLC ±0.1
2 PLC ±0.1
3 PLC ±
4 PLC ±
ANGLES ±1°

MATERIAL –
FINISH –

DWN Raghavendra.M 11OCT2021
CHK S.Aboulkassem 13DEC2021
APVD C.Schrettlinger 13DEC2021
PRODUCT SPEC 108-94515
APPLICATION SPEC – △4
WEIGHT SEE TABLE

TE Connectivity

NAME MATE-AX, 90DEG, CENTER CONTACT CABLE SIDE
–

SIZE A2 | CAGE CODE 00779 | DRAWING NO C-2327554 | RESTRICTED TO –


CUSTOMER DRAWING | SCALE 10:1 | SHEET 1 OF 2 | REV C


Downloaded from Arrow.com.


© 2021 TE Connectivity. All Rights Reserved.


CENTER CONTACT 2327554-2, RG174
Innenleiter Kontakt 2327554-2, RG174

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-











SECTION B-B
20:1



UNW INDING DIRECTIONA
Abwickelrichtung



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Raghavendra.M 11OCT2021	TE Connectivity
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.2, 1 PLC ±0.1, 2 PLC ±0.1, 3 PLC ±, 4 PLC ±, ANGLES ±1°	CHK S.Aboulkassem 13DEC2021	NAME MATE-AX, 90DEG, CENTER CONTACT CABLE SIDE -
		APVD C.SchrettLinger 13DEC2021	
		PRODUCT SPEC 108-94515	
		APPLICATION SPEC - (4)	SIZE A2 / CAGE CODE 00779 / DRAWING NO C-2327554 / RESTRICTED TO -
MATERIAL - -	FINISH - -	WEIGHT SEE TABLE	
		CUSTOMER DRAWING	SCALE 10:1 / SHEET 2 OF 2 / REV C

Downloaded from Arrow.com.