




APPROVED: _____
DATE: _____ TITLE: _____



SCHEMATIC

ASJ-15-3	ASJ-15-3A	ASJ-15-4A	ASJ-15-4B	ASJ-15-5

SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy

Plating:

Tin over Copper underplate

Electrical:

Operating voltage: 30 VDC max.

Current rating: 0.5 Amp max.

Contact resistance: 30 mohms max. initial

Insulation resistance: 100 Mohms min.

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -65°C to +125°C

Environmental:

Lead free, RoHS compliant.



Rev	AWO #	Description	Date	Appr
-		RELEASED	04/08/05	
A		REDREW	6/27/08	

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE: STEREO JACK, 3.5mm, RIGHT ANGLE
SURFACE MOUNT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				INCHES				Holes			
.X	± .10	ØX	± .10	.X	± .10	ØX	± .10	.X	± .10	ØX	± .10
.XX	± .020	ØXX	± .015	.XX	± .020	ØXX	± .015	.XX	± .015	ØXX	± .010
.XXX	± .015	ØXXX	± .010	.XXX	± .015	ØXXX	± .010	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE							
DRAWN				SS				04/08/05			
CHECKED											
APPROVED											
SIZE				PART NO.				ASJ-15-XX			
REF:				SCALE: NTS				SHEET 1 OF 1			