

PAX-327

27" FHD Surgical Monitor



Features

- True Flat Design with AR Filter
- High Brightness and High Contrast Ratio
- FHD Resolution (1920 x 1080)
- HDMI 2.0, DP 1.2, DVI, RGB Support Up to (1920 x 1080) @ 60 Hz
- SDI Support Up to 1920 x 1080 @ 60Hz
- Multi-Standard Video System Supported: NTSC, PAL, SECAM
- Video Enhancement features including:
 - 14-bit LUT processing
 - DICOM Part 14 GSDF Compliant
 - DICOM, Clear, Blue modes support
- Optional upgrade to IP-based monitor with AVAS



Introduction


PAX-3 series are medical certified displays for use in operating room imaging applications such as endoscopy, laparoscopy and other imaging modalities. With multiple I/O and support for 14-bit look up table, DICOM and gamma calibrations ensure accurate and precise image reproduction.

Specifications

		PAX-327-C2B-HAS PAX-327-C2B-HAR PAX-327-C2F-HAS PAX-327-C2B-HAS-WL	PAX-327-C2B-LAS PAX-327-C2B-LAR PAX-327-C2C-LAS PAX-327-C2K-LAS PAX-327-C2F-LAS
LCD	Screen Size	27" (597.89 x 336.31 mm)	
	Resolution	1920 x 1080	
	Aspect Ratio	16:9	
	Pixel Pitch	0.3114 x 0.3114 mm	
	Viewing Angle	178° / 178°	
	Contrast Ratio (Typ.)	1000 : 1	
	Native Luminance (Typ.)	900 nits (cd/m²)	300 cd/m²
	Color Depth	10-bit 1.07B Colors	8-bit 16.7M Colors
	Display Mode	AHVA	AHVA / ADS
	Response Time	14ms (Tr + Tf)	14ms (Gray to Gray)
	Touchscreen	Optional 10-point PCAP	
Input	Backlight	LED	
	DP 1.2 Input	DP Jack x 1	DisplayPort 1.2, 1920 x 1080 @ 60Hz max.
	HDMI 2.0 Input	HDMI Jack x 1 (Type A)	Digital RGB: TMDS, 1920 x 1080 @ 60Hz max.
	DVI Input	DVI Jack x 2 (Type D)	Digital RGB: TMDS, 1920 x 1080 @ 60Hz max.
	SDI1 Input	BNC Jack x 1	Serial Input Common Mode: 2.2 Vp-p (75 Ω); 1920 x 1080 @ 60 Hz max.
	S-Video Input	Mini DIN Jack x 1 (4-pin)	Y: 1 Vp-p (75 Ω), C: 0.286 Vp-p (75 Ω) [NTSC] Y: 1 Vp-p (75 Ω), C: 0.300 Vp-p (75 Ω) [PAL / SECAM]
	Video Input	BNC Jack x 1	1 Vp-p (75 Ω) [NTSC / PAL / SECAM]
	USB Up	USB-B Jack x 1	For Optional Touchscreen
	RS-232C	Mini DIN Jack x 1 (8-pin)	Service Port
	DC Power Input	DC Jack x 1	DC 24 V, 4.16 A
Optional Input	RGB Input	D-sub x 1	PAX-327-C2B-HAS, PAX-327-C2B-HAR, PAX-327-C2B-LAR, PAX-327-C2B-LAS, PAX-327-C2B-HAS-WL, PAX-327-C2C-LAS
	Audio Input	Audio Jack x 1	
	AVAS NDCoder	SFP+ Module x 1 LAN RJ-45 Jack x 1	PAX-327-C2F-HAS, PAX-327-C2F-LAS
	SDI2 Input	BNC Jack x 1	PAX-327-C2C-LAS, PAX-327-C2K-LAS
	Wireless HDMI	Built in Wireless HDMI Receiver	PAX-327-C2B-HAS-WL
Output	DVI Output	DVI Jack x 2 (Type D)	Digital RGB: TMDS, 1920 x 1080 @ 60 Hz max
	SDI1 Output	BNC Jack x 1	Serial Input Common Mode: 2.2 Vp-p (75 Ω); 1920 x 1080 @ 60 Hz max.
	S-Video Output	Mini DIN Jack x 1 (4-pin)	Y: 1 Vp-p (75 Ω), C: 0.286 Vp-p (75 Ω) [NTSC] Y: 1 Vp-p (75 Ω), C: 0.300 Vp-p (75 Ω) [PAL / SECAM]
	Video Output	BNC Jack x 1	1 Vp-p (75 Ω) [NTSC / PAL / SECAM]
	DC Power Output	DC Jack x 1	DC 5 V or DC 12 V
Optional Output	Audio Output	Audio Jack x 1	PAX-327-C2B-HAS, PAX-327-C2B-HAR, PAX-327-C2B-LAR, PAX-327-C2B-LAS, PAX-327-C2B-HAS-WL, PAX-327-C2C-LAS
	SDI2 Output	BNC Jack x 1	PAX-327-C2C-LAS, PAX-327-C2K-LAS
Environment	Temperature	Operational	0 ~ 40 °C
		Storage	-20 ~ 60 °C
	Humidity	Operational	Ta = 40 °C, 90% RH non-condensed
		Storage	5 ~ 90%
	Pressure	Operational	500 hPa to 1013 hPa
		Storage	500 hPa to 1013 hPa
Power	Rating	DC 24 V, 4.16 A max.	
	Consumption (Typ.)	77.3W max.	
Physical Characteristics	IP Ratings	Front IP65 / Top IPX1	
	VESA Mount	100 x 100; 75 x 75 mm	
	Dimension (W x D x H)	663.83 x 73.55 x 418.11 mm	
	Weight	9.6kg max	
Certifications		CE MDR (EN60601-1; EN60601-1-2), RoHS II	
Warranty		3 Years	
Accessories		Power Adapter	

Dimensions

Unit: mm



Ordering Information

Part Number	Brightness	Optional	Touchscreen	Weight
PAX-327-C2B-HAS	900 nits (cd/m ²)	RGB/Audio	-	8.9 kg
PAX-327-C2B-HAR	900 nits (cd/m ²)	RGB/Audio	PCAP	8.9 kg
PAX-327-C2F-HAS	900 nits (cd/m ²)	AVAS	-	9.2 kg
PAX-327-C2B-LAS	300 cd/m ²	RGB/Audio	-	8.9 kg / 9.3 kg
PAX-327-C2B-LAR	300 cd/m ²	RGB/Audio	PCAP	8.9 kg / 9.3 kg
PAX-327-C2B-HAS-WL	900 nits (cd/m ²)	RGB/Audio/Wireless HDMI	-	9.4 kg
PAX-327-C2C-LAS	300 cd/m ²	RGB/Audio/SDI2	-	9.0 kg / 9.4 kg
PAX-327-C2K-LAS	300 cd/m ²	SDI2	-	9.0 kg / 9.4 kg
PAX-327-C2F-LAS	300 cd/m ²	AVAS	-	9.2 kg / 9.6 kg

Optional Items


Part Number	Description
1702002605	Power Cord (Europe) 1.8M
1702002600	Power Cord (USA) 1.8M
1700018704	Power Cord (UK) 1.8M
XKT-HPU101-P09B139	Power Adapter AC/DC 100-240V 100W 24V DIN 4PIN MEDICAL

Recommended Mounting Solution

Model Name	ARES-2423R	
Part Number	ARES-2423R-A741L00	ARES-2423R-A741L01
Photo		
Max. Support Weight	6 - 12kg	
Max. Support Panel Size	≤ 27"	
VESA Information	75 x 75 mm 100x100 mm	

For more information, please click this link: <https://bit.ly/3T7dLMR>

Front Function Keys



1. POWER button/indicator
2. ENTER/MENU button
3. EXIT/INPUT button
4. LEFT button
5. RIGHT button
6. PIP INPUT select buttons
 - A. Main input
 - B. Sub input