



FEATURES:

- Slim retractable probe is fully insulated to within 1/8" of tip.
- Needle point tip adjusts to desired length from 0 to 3" (0 to 76mm)
- Stainless steel needle sharp point easily pierces varnish and thin insulation.
- Tip can be re-pointed if necessary.
- Shrouded banana plug is designed to fit most popular digital multimeter jacks.
- Banana plug molded directly to the wire for robust pull strength.
- Banana plug spring is nickel plated Beryllium Copper for long insertion life.
- 4-foot test lead wire is silicone insulated for high temperature resistance. Also remains flexible at low temperature

MATERIALS:

Probe: Polypropylene and PVC, black and red

Tip: Stainless steel

Wire: 20 AWG, Silicone insulation

RATINGS:

UL-3111, EN61010-2-031, IEC 1010-2-031, Cat II 600V

Operating Voltage: 600 Max

Current: 3 Amperes

ORDERING INFORMATION: Model 5953A

Includes a set of one black and one red test lead

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

PomonaACCESS 90811 (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com

Page 1 of 1