Datasheet for part number ECCE2021-050S0A-EJCV0A

Our Catalog Part Number: ECCE2021-050S0A-EJCV0A
Our Global Manufacturing Part Number: 132056-9008
Brand: Cannon Product Category: EV Product Line: EV Series: EV

Product Datasheet	
Series	EVC IEC 62196 Type 2 mode 3 connection cable
Product Image	Current Rating
20A	Cable Rating
Level 2	Powering System
Single phase (250VAC)	Cable Length
5 m	Direction of Cable Strain Relief
Straight cable strain relief	Dust Cap
No dust cap	Modification Code 2nd Connector
Connection cable IEC Type 1 connector on 2-end (same as J2CE)	Direction of Cable Outlet
Straight cable strain relief	Temperature Range
-30°C to +50°C	Durability
10,000 mating cycles min	Sealing Requirements
IP 44 min per IEC 61851-1 and tested in accordance with IEC 60525	Certifications Connector
CE, ETL, IEC 62196-1 and IEC 62196-2	Certifications Cable
DIN EN 50620	Product Drawing

Specifications and dimensions subject to change.

Downloaded from Arrow.com.