

Gigabit Ethernet Passive 24V @ 1000mA

Gigabit 24V Passive Power Over Ethernet Injector



Model: PoEGP2408

KEY FEATURES

- The Gigabit Power over Ethernet (PoE) Injector provides power over a distance of up to 100 meters (328 ft.)
- Full Duplex Gigabit speeds supported
- Supplies power up to 24 Watts
- Universal Input 100 to 240VAC
- RoHS Compliant
- Meet ErP / Energy Star. Level : V Standards
- Meet EN55022/ EN55024 Standards

Specifications

Output Voltage	24V DC @ 1000mA
Power Consumption	24 Watts (Max)
Efficiency	70%
Line Regulation	+/- 1%
Load Regulation	+/- 3%
MTBF	50,000 hours
Standard	IEEE 802.3 10Base-T IEEE 802.3u 100Base-TX IEEE 802.3ab Gigabit Ethernet
Network Media	10Mbps: UTP/STP Cat. 5 and 5e up to 100 Meters 100Mbps: UTP/STP Cat. 5, and 5e up to 100 Meters Gigabit: UTP/STP Cat 5e and 6 up to 100 meters
Ports	1 x 10/100/1000Mbps DATA-IN (Data only) 1 x 10/100/1000Mbps PWR+DATA-OUT
RoHS Compliance	Yes
Environmental	Temperature: Operating: 0°C to 40°C, Storage: -25°C to 65°C Humidity (non-condensing): Operating: 10% to 90%, Storage: Max. 90%
Certification	CE
Dimension (W x H x D)	115 x 50 x 31 mm

Mechanical Dimensions

