44AM1111-16-9-9 Product Details



44AM1111-16-9-9

TE Internal Number: 301015-000

Active

Spec 44, Spec 55 and Spec RCW Wire and Cable

Not EU RoHS or ELV Compliant

Product Highlights:

- Cable Type = Spec 44
- Wire Source = United States
- Cable Style = Jacketed, Round-Braid Shielded
- Wire Size (AWG/CM) = 16 AWG
- Voltage Rating = 600 VAC

View all Features

Add to My Part List | Request Sample | Find Similar Products | Buy Product

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Documentation & Additional Information

Product Drawings:
- Customer Drawing (PDF, English)

Catalog Pages/Data Sheets:
- None Available

Product Specifications:
- None Available

Application Specifications:
- None Available

Instruction Sheets:
- None Available

CAD Files:
- None Available

List all Documents

Additional Information:
- Product Line Information

Related Products:
- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:
- Cable Type = Spec 44
- Cable Style = Jacketed, Round-Braid Shielded
- Number of Conductors = 1

Electrical Characteristics:
- Voltage Rating (VAC) = 600

Body Related Features:
- Wire Size (AWG/CM) = 16 AWG
- Cable Jacket Color = White
- Conductor Type = Tin-Plated Copper
- Wire Color = White

Industry Standards:
- RoHS/ELV Compliance = Not ELV/RoHS compliant
- Lead Free Solder Processes = Not relevant for lead free process

Conditions for Usage:
- Temperature Range (°C) = -65 – +150

Operation/Application:
- Application = General Purpose

Packaging Related Features:
- Wire Source = United States

Other:
- Brand = Raychem

© 2010 Tyco Electronics All Rights Reserved | Privacy Policy

Downloaded from Arrow.com.