Datasheet for part number NLDFT-E-GN-L-S120-M40S

Our Catalog Part Number: NLDFT-E-GN-L-S120-M40S
Our Global Manufacturing Part Number: 078238-0604
Brand: Cannon Product Category: Circular Product Line: Veam Powerlock & Snaplock Series: POWERLOCK

Product Datasheet	
Series	Line Drain (female contact)
Shell Style	Earth
Color	Green
Locking Type	Secondary Locking pin fitted to Drain Connector
Contact Type	120 mm set screw
Cable Gland	M40S cable gland (Cable OD 15-23 mm)
Maximum current rating	400 A
Maximum rated voltage to earth	2KVac / 3KVdc
Minimum flashover	9.5K Vdc or Ac peak
Operating temperature range	-30°/+125°
Insulation resistance	<5 M ohms @500Vdc
Ingress protection (mated)	IP67
Protection against electrical shock	IP2X
Flammability	UL94-V0
Contact Retention	Nylon Pin
Mating Method	Bayonet
Mating Cycles	500
Operating Voltage	1000Vac
Shell Material Finish	High temperature thermoplastic

Specifications and dimensions subject to change.

Downloaded from Arrow.com.