

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0934442209

Status: Active

Overview: ML-XT Sealed Connection System

Description: ML-XT Sealed 3 Circuit Receptacle Housing, Pre-Assembled with Large Rear Seal and Cover, Red



Documents:

3D Model	Application Specification 934430010-A (PDF)
Drawing (PDF)	Packaging Specification 934430002-K (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 934430010-P (PDF)	Product Literature (PDF)

Agency Certification	
UL	E29179
General	
Product Family	Crimp Housings
Series	93444
Application	Power, Signal, Wire-to-Wire
Overview	ML-XT Sealed Connection System
Product Literature Order No	987651-0201
Product Name	ML-XT
UPC	889056313636
Physical	
Circuits (maximum)	3
Color - Resin	Red
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	6.872/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Temperature Range - Operating	-55° to +125°C
Electrical	
Current - Maximum per Contact	13.0A
Material Info	
Reference - Drawing Numbers	
Application Specification	934430010-A
Packaging Specification	934430002-K
Product Specification	934430010-P
Sales Drawing	934430020-000

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

93444 Series

Mates With

ML-XT Sealed 3 Circuit Plug Housing
934452209

Use With

ML-XT Male (Pin) Terminal 845240004
(Nickel), ML-XT Male (Pin) Terminal
845240014 (Selective Gold), ML-XT 3
Circuit Receptacle Wedgelock 93447 , ML-
XT Blind Cavity Plug 934941000

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION