

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0151660123
Status: Active
Overview: Premo-Flex™ Cable Jumpers
Description: 0.50mm Pitch Premo-Flex™ FFC Jumper, Same Side Contacts (Type A), 12 Circuits, 0.102m Cable Length, Cable Thickness 0.12mm, Tin (Sn) Plating

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-15166-001-001 \(PDF\)](#)
[Packaging Specification PK-15166-001-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Cable
Series 15166
Comments Contacts on the same side, Type A
Crimp Quality Equipment Yes
Overview Premo-Flex™ Cable Jumpers
Product Name Premo-Flex™FFC Jumper
UPC 884982846159

Physical
Cable Length 0.102m
Circuits (Loaded) 12
Circuits (maximum) 12
Net Weight 1.000/g
Packaging Type Bag
Pitch - Termination Interface 0.50mm
Temperature Range - Operating -40°C to +105°C
Wire Size AWG N/A
Wire/Cable Type Flat Flex Cable

Electrical
Current - Maximum per Contact 0.5A
Voltage - Maximum 60V AC

Material Info

Reference - Drawing Numbers
Packaging Specification PK-15166-001-001
Product Specification PS-15166-001-001
Sales Drawing SD-15166-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[15166 Series](#)

Use With
Molex FFC – FPC connector. Be sure to match like plating.

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION