

Product data sheet

Specifications

APC IT Power Distribution Module 3 Pole 5 Wire 16A IEC309 260cm



PDM3516IEC-260

Overview

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
--------------	--

Lead time	Usually Ships within 3 Weeks
-----------	------------------------------

Main

Main Input Voltage	400 V 3 phases
Main Output Voltage	230 V 400 V 3 phases
Provided equipment	Installation guide

Physical

Colour	Grey
Height	15.2 cm
Width	43.2 cm
Depth	40.6 cm
Net weight	1.79 kg

Input

Network frequency	50 Hz
Max line current	16 A

Output

Max current draw	16 A
Number of power socket outlets	1 IEC 309 16 A

Conformance

Product certifications	CE VDE
------------------------	-----------

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	15.2 cm
Package 1 Width	40.6 cm
Package 1 Length	43.2 cm
Package 1 Weight	2.7 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------

Recommended replacement(s)